



INTIMAC S.R.L.

Via XXV Aprile, 8
21054 Fagnano Olona (VA) - Italia
Tel. +39 0331 1693557
email: inti@intisrl.it


Complete Lines BOSCH RRU 3043 +HQL 2440S +ALF 4060 +DRN 3010 +FLC 3060 + VRK 2005

Images

Product details

Category:	Sold
Machine:	RRU 3043 +HQL 2440S +ALF 4060 +DRN 3010 +FLC 3060 + VRK 2005
Machine code:	22-588
Manufacturer:	BOSCH
Year of construction:	2005

Description



Bosch line for ampoules and vials from 2005 including the following machines :

RRU 3043 +HQL 2440S +ALF 4060 +DRN 3010 +FLC 3060 + VRK 2005

1. bosch vials washing machine RRU 3043

technical specifications

Length 2240 mm Width mm 2130 Height 1700 mm

Net weight Kg 2000

Maximum container diameter 52 mm

Maximum container height 128 mm

Maximum output 12000 / hour

2. Depyrogenation Tunnel Bosch HQL 2440S

HQL installations are ideal for the sterilisation of vials. This model is exceptional because of the low throughput in the tunnel, which is the result of the laminar hot air flow process with its high degree of efficiency. The cooling section operates with laminar flow.

Safe conveyor belts on floor and side levels operated simultaneously. Excellent accessibility and ease of operation.

3. Filling/capping machine Bosch ALF 4060

- Output max. 18,000 ampoules/h

- Pre/post gassing

- Filling

- Preheating

- Capping via spit take-off, closing gassing

- Manual in-process control (IPC)

- Storage of containers in discharge magazine

- Included format sets (diameter): 1 ml, 10.75 ; 2 ml, 10.75 ; 5 ml, 14.75; 10 ml, 17.75

4. Color Ring Printer Bosch DRN 3010

This high-speed machine is design to mark ampoules with single or multiple ring codes. It is useful for identifying trial batches or for adding colour codes to standard batches of Ampoules for identification purposes or to avoid intermixing of batches.

- Included format sets (diameter) : 1 ml, 10.75 ; 2 ml, 10.75 ; 5 ml, 14.75; 10 ml, 17.75

5. Bosch Vials Filler FLC 3060

The continuous motion machine provides a processing range with filling volumes of 0.5 - 500 ml. A "V-cleat" conveyor system offers advantages in ease of size changeover

Filling programs can be stored and recalled via the control panel.

Technical data :

Containers: Injection vials and infusion bottles made of glass and plastic, up to 500 ml.

Diameter 14 - 86 mm

Height 30 - 180 mm

Pharmaceutical liquids (e.g. hydrous solutions, suspensions).

Closures: Rubber stoppers (siliconized or teflonized) in mushroom or freeze dry version

Speed 12.000 vials per hour

6. Bosch Crimping Machine VRK 2005

The VRK 2005B works continuously and has a 5-head capping station with a separate drive for container rotation from the main transport drive and other functions. The VRK 2005 B is commonly implemented in-line with Bosch filling and closing machines such as the MLF, FLC and FLM machines, boasting a very high technology profile.

Processing range:

Container Ø (mm): 13.75-86

Container height (mm): 35-180

Max output per hour: 12.000